GRYPHON[™] 4500 HEALTHCARE ↔DATALOGIC

Premium handheld scanners for corded or cordless value added Healthcare applications



THE PURPOSE OF BAR CODE READERS IN THE HEALTHCARE INDUSTRY

The key mission of scanners in the healthcare industry is to improve the quality of patient care while reducing medication errors. Additionally, healthcare environments have requirements that scanners need to be regularly cleaned and disinfected. The Datalogic Gryphon[™] HC product series is specifically developed for healthcare applications with Disinfectant-Ready enclosures treated with antimicrobial additives and are designed to withstand daily cleaning with harsh disinfectant solutions.

The Gryphon 4500-HC 2D readers can decode virtually any 1D and 2D bar code symbology and can read codes from LCD monitors, cell phones, smartphones and other mobile devices. High Density (HD) models are also available for reading smaller, condensed codes.

Ideally suited for stationary applications in administration, laboratory and hospital environments, the GD4500-HC 2D desktop model offers an affordable corded solution, while the GM4500-HC 2D or GBT4500-HC 2D cordless models (STAR or Bluetooth®) provide extended mobility for cordless operations.

Datalogic's distinctive reading technology with highly visible white or red-illumination is easier on the human eyes and reads colored labels better. The highly visible 4-Dot aimer provides a clear indication of the reading area, making targeting codes quick and easy. Datalogic's patented 'Green Spot' technology provides additional visual good-read confirmation which is ideal for quiet environments such as bedside patient care.

The vibration option coupled with the silent operating mode can also be set to further increase the patients' comfort.

One of the most important technical innovations that the Gryphon 4500 wireless readers achieve is the wireless charging system for the battery, which enhances the reliability of the entire solution, while lowering the total cost of ownership (no need for contact cleaning or maintenance procedures).

PRODUCT	CHEMICAL CONTENT
Sani-Cloth® HB, Sani-Cloth® Plus, Super Sani-Cloth®	Quaternary Ammonium Chloride solution
Hepacide Quat II	Virucidal disinfectant cleaner
Alcohol Wipes	70% Isopropyl Alcohol
CaviWipes™	Isopropanol 10-20%; Ethylene Glycol Monobutyl Ether 1-5%
Virex® 256	n-Alkyl Dimethyl Benzyl Ammo- nium Chloride; Didecyl Dimethyl Ammonium Chloride
Formula 409® Glass and Surface Cleaner	n-Alkyl Dimethyl Benzyl Ammoni- um Chloride; n-Propoxypropanol
Windex® Blue	Isopropyl Alcohol
Clorox® Bleach; Clorox Healthcare Bleach Germicidal Cleaner	Sodium Hypochlorite; Sodium Hydroxide
Hydrogen Peroxide	3%
ProSpray™ Wipes (Disinfectant towelettes)	0.647% o-phenylphenol; 0.070% o-benzyl-p-chlorophenol
100% Gentle dish soap and water	



FEATURES

- Disinfectant-Ready enclosures treated with anti-microbial additives (ISO22196 compliant) withstand daily cleaning with harsh disinfectant solutions
- 1 MP optics for superior scanning and Depth of Field
- Extended reading distances and snappy reading of small, condensed, curved, poorly printed, and reflective bar codes
- Highly visible 4-Dot aimer with center cross for targeted scanning
- Datalogic's 'Green Spot' technology, exclusive 3GL™ (3 Green Lights) and Vibration for superior good-read feedback
- Motionix[™] motion-sensing technology for seamless reading mode transitions
- Image capture and document scanning capabilities
- Omnidirectional reading of 1D, 2D and postal codes plus stacked, composite codes and dot codes
- Choice of Bluetooth wireless technology version or Datalogic's STAR Cordless System (radio frequencies available in 433 MHz or 910 MHz)
- Wireless battery charging system
- Choice of WLC4090 adjustable position cradle with Scan-While-Charging capability or WLC4190 sleek desk/wall cradle with USB Type C connectivity



GRYPHON 4500 HEALTHCARE SERIES TECHNICAL SPECIFICATIONS

CORDLESS MODELS COMMUNICATIONS

CORDLESS MODELS COMMUNICATIONS		
Gryphon GBT4500	Bluetooth Wireless Technology Piconet: Max. 7 readers per radio receiver (cradle and commercial dongle); Profiles: HID (Human Interface Device); SPP (Serial Port Profile); Protocol: Bluetooth 5.0 Certified Class 1, Class 2 and Class 3; Radio Frequency: 2.4 GHz; Radio Range (Open Air): 100.0 m / 328.0 ft; Range distances are measured using the base station. Range with connection to other Bluetooth peripherals may show different results. Security: Data Encryption; Scanner Authentication	
Gryphon GM4500	Datalogic STAR Cordless System Effective Radiated Power: 433.92 MHz: < 6.3 mW; 910 MHz: < 50 mW; Multi-Point Configuration: Max. Readers per Radio Receiver: 16; Point-to-Point Configuration; Radio Frequency: 433.92 MHz; 910 MHz; Two Way Communications Radio Range (Open Air): 50.0 m / 164.0 ft	
DECODING CAPABII	_ITY	
1D / Linear Codes	Auto discriminates all standard 1D codes including GS1 DataBar™ linear codes.	
2D Codes	Aztec Code; China Han Xin Code; Data Matrix; MaxiCode; Micro QR Code; QR Code; Dot Code	
Postal Codes	Australian Post; British Post; China Post; IMB; Japanese Post; KIX Post; Planet Code; Postnet; Royal Mail Code (RM4SCC)	
Stacked Codes	EAN/JAN Composites; GS1 DataBar Composites; GS1 DataBar Expanded Stacked; GS1 DataBar Stacked; GS1 DataBar Stacked Omnidirectional; MacroPDF; MicroPDF417; PDF417; UPC A/E Composites	
CORDLESS MODELS ELECTRICAL		
Battery	Battery Type: Lithium-Ion: 3250 mAh Charge Time: External Power: 4 Hours @ 12 VDC; Reads per Charge: 80,000	
Cradle Indicator LEDs	Battery Charging (flashing orange); Charge Completed (steady green)	
Current	Charging (Typical): < 6 W; Scanner only: 330 mA @ 3.7 V (Operative) Cradle only: 80 mA @ 5 V (Operative)	
Input Voltage (Cradle)	4.5 - 14 VDC +/- 5% (WLC4090/WLC4190)	
CORDED MODELS E	LECTRICAL	
Current	Operating: <400 mA @ 5V; < 200 mA @ 12V Standby/Idle: < 90 mA @ 5V; <50 mA @ 12V	
Input Voltage	GD4520: 5 VDC; GD4590: 4.5 - 14.0 VDC	
ENVIRONMENTAL		
Ambient Light	0 - 100,000 lux	
Drop Resistance	Withstands repeated drops from 1.8 m / 6.0 ft onto a concrete surface.	
ESD Protection (Air Discharge)	16 kV	
Humidity (Non-Condensing)	0 - 95%	
Particulate and Water Sealing	IP52 Operating: 0 to 50 °C / 32 to 122 °F	
Temperature	Storage/Transport: -40 to 70 °C / -40 to 158 °F	
INTERFACES		
Interfaces	CORDLESS MODELS: WLC4090: USB / RS-232 Multi-Interface WLC4190: USB Type C / USB / RS-232 Multi-Interface CORDED MODELS: GD4520: USB Type C / USB only GD4590: USB Type C / USB / RS-232 Multi-Interface	

PHYSICAL CHARAC	TERISTICS		
Colors Available	Black, White (with light green plastic/rubber details)		
Dimensions	16.6 x 6.8 x 10.9 cm / 6.5 x 2.7 x 4.3 in (corded/cordless models)		
Weight	161 g / 5.7 oz (corded models); 235 g / 8.29 oz (cordless models, battery included)		
Enclosure	Disinfectant-Ready enclosure treated with anti-microbial additives (ISO22196 compliant)		
READING PERFORM	1ANCE		
Image Capture	Graphic Formats: BMP, JPEG, TIFF; Greyscale: 256, 16, 2		
Imager Sensor	1 Megapixel: 1280 x 800 pixels		
Light Source	Aiming: Red Laser 650 nm Illumination: Warm White; Hyper Red LED on specific models		
Motion Tolerance	35 IPS		
Print Contrast Ratio (Minimum)	15%		
Reading Angle	Pitch: +/- 65°; Roll (Tilt): 360°; Skew (Yaw): +/- 65°		
Reading Indicators	Beeper (adjustable tone); Datalogic Three Green Lights (3GL) Good-read feedback: Datalogic 'Green Spot' on the Code, Dual Good-read LEDs; Vibration feedback option available on cordless models		
Resolution (Maximum)	High Density (HD): 1D Linear: 0.077 mm / 3 mils; PDF417: 0.077 mm / 3 mils; Data Matrix: 0.102 mm / 4 mils Standard Range (SR): 1D Linear: 0.102 mm / 4 mils; PDF417: 0.127 mm / 5 mils; Data Matrix: 0.195 mm / 7.5 mils		
READING RANGES			
Typical Depth of Field	Minimum distance determined by symbol length and scan angle. Printing resolution, contrast, and ambient light dependent.		
EAN/UPC: 13 mils: 1.0 to 71.0 cm / 0.4 to 27.9 in EAN/UPC: 7.5 mils: 2.0 to 23.5 cm / 0.8 to 9.3 PDF417: 10 mils: 2.5 to 41.0 cm / 1.0 to 16.1 in EAN/UPC: 13 mils: 1.0 to 40.0 cm / 0.4 to 15. QR Code: 10 mils: 5.5 to 24.0 cm / 2.2 to 9.5 in PDF417: 10 mils: 0.5 to 31.0 cm / 0.2 to 12.2 in		Code 39: 3 mils: 5.0 to 15.0 cm / 2.0 to 5.9 in Code 39: 5 mils: 0.5 to 25.0 cm / 0.2 to 9.8 in	
EAN/UPC: 13 mils: 1.0 to 71.0 cm / 0.4 PDF417: 10 mils: 2.5 to 41.0 cm / 1.0	4 to 27.9 in to 16.1 in	Data Matrix: 10 mils: 2.0 to 27.0 cm / 0.8 to 10.6 in EAN/UPC: 7.5 mils: 2.0 to 23.5 cm / 0.8 to 9.3 in EAN/UPC: 13 mils: 1.0 to 40.0 cm / 0.4 to 15.7 in	
EAN/UPC: 13 mils: 1.0 to 71.0 cm / 0.4 PDF417: 10 mils: 2.5 to 41.0 cm / 1.0	4 to 27.9 in to 16.1 in to 9.5 in	Data Matrix: 10 mils: 2.0 to 27.0 cm / 0.8 to 10.6 in EAN/UPC: 7.5 mils: 2.0 to 23.5 cm / 0.8 to 9.3 in EAN/UPC: 13 mils: 1.0 to 40.0 cm / 0.4 to 15.7 in PDF417: 4 mils: 3.0 to 12.0 cm / 1.2 to 4.7 in PDF417: 10 mils: 0.5 to 31.0 cm / 0.2 to 12.2 in	
EAN/UPC: 13 mils: 1.0 to 71.0 cm / 0.4 PDF417: 10 mils: 2.5 to 41.0 cm / 1.0 QR Code: 10 mils: 5.5 to 24.0 cm / 2.2	to 27.9 in o 16.1 in to 9.5 in TORY The product meet approvals for its The Quick Refere	Data Matrix: 10 mils: 2.0 to 27.0 cm / 0.8 to 10.6 in EAN/UPC: 7.5 mils: 2.0 to 23.5 cm / 0.8 to 9.3 in EAN/UPC: 13 mils: 1.0 to 40.0 cm / 0.4 to 15.7 in PDF417: 4 mils: 3.0 to 12.0 cm / 1.2 to 4.7 in PDF417: 10 mils: 0.5 to 31.0 cm / 0.2 to 12.2 in QR Code: 10 mils: 2.0 to 25.0 cm / 0.8 to 9.8 in ets necessary safety and regulatory	
EAN/UPC: 13 mils: 1.0 to 71.0 cm / 0.4 PDF417: 10 mils: 2.5 to 41.0 cm / 1.0 QR Code: 10 mils: 5.5 to 24.0 cm / 2.2 SAFETY & REGULA	to 27.9 in o 16.1 in to 9.5 in TORY The product mee approvals for its The Quick Reference referred to for a	Data Matrix: 10 mils: 2.0 to 27.0 cm / 0.8 to 10.6 in EAN/UPC: 7.5 mils: 2.0 to 23.5 cm / 0.8 to 9.3 in EAN/UPC: 13 mils: 1.0 to 40.0 cm / 0.4 to 15.7 in PDF417: 4 mils: 3.0 to 12.0 cm / 1.2 to 4.7 in PDF417: 10 mils: 0.5 to 31.0 cm / 0.2 to 12.2 in QR Code: 10 mils: 2.0 to 25.0 cm / 0.8 to 9.8 in ets necessary safety and regulatory intended use. ence Guide for this product can be	
EAN/UPC: 13 mils: 1.0 to 71.0 cm / 0.4 PDF417: 10 mils: 2.5 to 41.0 cm / 1.0 QR Code: 10 mils: 5.5 to 24.0 cm / 2.2 SAFETY & REGULA Agency Approvals	to 27.9 in o 16.1 in to 9.5 in TORY The product mee approvals for its The Quick Refer referred to for a Complies to Chir	Data Matrix: 10 mils: 2.0 to 27.0 cm / 0.8 to 10.6 in EAN/UPC: 7.5 mils: 2.0 to 23.5 cm / 0.8 to 9.3 in EAN/UPC: 13 mils: 1.0 to 40.0 cm / 0.4 to 15.7 in PDF417: 4 mils: 3.0 to 12.0 cm / 1.2 to 4.7 in PDF417: 10 mils: 0.5 to 31.0 cm / 0.2 to 12.2 in QR Code: 10 mils: 2.0 to 25.0 cm / 0.8 to 9.8 in ets necessary safety and regulatory intended use. ence Guide for this product can be complete list of certifications. ha RoHS; Complies to EU RoHS adiation - Do not stare into beam;	
EAN/UPC: 13 mils: 1.0 to 71.0 cm / 0.4 PDF417: 10 mils: 2.5 to 41.0 cm / 1.0 QR Code: 10 mils: 5.5 to 24.0 cm / 2.2 SAFETY & REGULA Agency Approvals Environmental Compliance	to 27.9 in o 16.1 in to 9.5 in The product meet approvals for its The Quick Referent referred to for a Complies to Chir Caution Laser R	Data Matrix: 10 mils: 2.0 to 27.0 cm / 0.8 to 10.6 in EAN/UPC: 7.5 mils: 2.0 to 23.5 cm / 0.8 to 9.3 in EAN/UPC: 13 mils: 1.0 to 40.0 cm / 0.4 to 15.7 in PDF417: 4 mils: 3.0 to 12.0 cm / 1.2 to 4.7 in PDF417: 10 mils: 0.5 to 31.0 cm / 0.2 to 12.2 in QR Code: 10 mils: 2.0 to 25.0 cm / 0.8 to 9.8 in ets necessary safety and regulatory intended use. ence Guide for this product can be complete list of certifications. ha RoHS; Complies to EU RoHS adiation - Do not stare into beam;	
EAN/UPC: 13 mils: 1.0 to 71.0 cm / 0.4 PDF417: 10 mils: 2.5 to 41.0 cm / 1.0 QR Code: 10 mils: 5.5 to 24.0 cm / 2.2 SAFETY & REGULA Agency Approvals Environmental Compliance Laser Classification	to 27.9 in o 16.1 in to 9.5 in TORY The product mee approvals for its The Quick Referce referred to for a Complies to Chir Caution Laser R IEC 60825 Class	Data Matrix: 10 mils: 2.0 to 27.0 cm / 0.8 to 10.6 in EAN/UPC: 7.5 mils: 2.0 to 23.5 cm / 0.8 to 9.3 in EAN/UPC: 13 mils: 1.0 to 40.0 cm / 0.4 to 15.7 in PDF417: 4 mils: 3.0 to 12.0 cm / 1.2 to 4.7 in PDF417: 10 mils: 0.5 to 31.0 cm / 0.2 to 12.2 in QR Code: 10 mils: 2.0 to 25.0 cm / 0.8 to 9.8 in ence Guide for this product can be complete list of certifications. na RoHS; Complies to EU RoHS adiation - Do not stare into beam; 2 n configuration program is available for	
EAN/UPC: 13 mils: 1.0 to 71.0 cm / 0.4 PDF417: 10 mils: 2.5 to 41.0 cm / 1.0 QR Code: 10 mils: 5.5 to 24.0 cm / 2.2 SAFETY & REGULA Agency Approvals Environmental Compliance Laser Classification UTILITIES	to 27.9 in o 16.1 in to 9.5 in TORY The product meet approvals for its The Quick Referent referred to for a Complies to Chir Caution Laser R. IEC 60825 Class Datalogic Aladdit download at no	Data Matrix: 10 mils: 2.0 to 27.0 cm / 0.8 to 10.6 in EAN/UPC: 7.5 mils: 2.0 to 23.5 cm / 0.8 to 9.3 in EAN/UPC: 13 mils: 1.0 to 40.0 cm / 0.4 to 15.7 in PDF417: 4 mils: 3.0 to 12.0 cm / 1.2 to 4.7 in PDF417: 10 mils: 0.5 to 31.0 cm / 0.2 to 12.2 in QR Code: 10 mils: 2.0 to 25.0 cm / 0.8 to 9.8 in ence Guide for this product can be complete list of certifications. na RoHS; Complies to EU RoHS adiation - Do not stare into beam; 2 n configuration program is available for	
EAN/UPC: 13 mils: 1.0 to 71.0 cm / 0.4 PDF417: 10 mils: 2.5 to 41.0 cm / 1.0 QR Code: 10 mils: 5.5 to 24.0 cm / 2.2 SAFETY & REGULA Agency Approvals Environmental Compliance Laser Classification UTILITIES Datalogic Aladdin™	TORY The product meet approvals for its The Quick Reference referred to for a Complies to Chir Caution Laser R IEC 60825 Class Datalogic Aladdi download at no JavaPOS and OF at no charge.	Data Matrix: 10 mils: 2.0 to 27.0 cm / 0.8 to 10.6 in EAN/UPC: 7.5 mils: 2.0 to 23.5 cm / 0.8 to 9.3 in EAN/UPC: 13 mils: 1.0 to 40.0 cm / 0.4 to 15.7 in PDF417: 4 mils: 3.0 to 12.0 cm / 1.2 to 4.7 in PDF417: 10 mils: 0.5 to 31.0 cm / 0.2 to 12.2 in QR Code: 10 mils: 2.0 to 25.0 cm / 0.8 to 9.8 in ence Guide for this product can be complete list of certifications. na RoHS; Complies to EU RoHS adiation - Do not stare into beam; 2 n configuration program is available for charge.	

5-Year Factory Warranty (corded models)

3-Year Factory Warranty (cordless models)

ACCESSORIES



Warranty

© 2019-2023 Datalogic S.p.A. and/or its affiliates. • All rights reserved. Without limiting the rights under copyright, no part of this documentation may be reproduced, stored in or introduced into a retrieval system, or transmitted in any form or by any means, or for any purpose, without the express written permission of Datalogic S.p.A. and/or its affiliates. • Datalogic logo are registered trademarks of Datalogic S.p.A. in many countries, including the U.S. and the E.U. • Datalogic STAR Cordless System, Motionix and 3GL are trademarks of Datalogic S.p.A. and/or its affiliates. • The Bluetooth word mark and logos are owned by Bluetooth SIG, Inc. and any use of such marks by Datalogic Group companies is under license. • All other trademarks and brands are property of their respective owner. • Product specifications are subject to change without notice. DS-GRYPHONA500-HC-SERIES-EN Rev H 20230906